

## POLABLE 141LRH

## One Side Treated Film


## Pearlized BOPP Film

## Features:

- Excellent opacity, gloss and stiffness
- Improved anti-static property
- Excellent dimensional stability eliminates wrinkles in hot melt bonding
- Excellent cutting characteristics on all types of roll-fed labelling machines

## Application:

- White voided BOPP film, specifically developed for single ply roll-fed bottle labels.
- It could be used for other kind of application such as cut & stack.



Specification	Test Method	Unit	Test Direction	38μ	55μ
Wetting Tension	ASTM D2578	Dyne/cm	Treated Side	≥ 36	
Tensile Strength	ASTM D882	N/mm <sup>2</sup>	MD	100	
			TD	190	
Elongation at Break	ASTM D882	%	MD	160	
			TD	35	
Thermal Shrinkage (120 °C, 5 min)	ASTM D1204	%	MD	≤ 4	
			TD	≤ 2	
Gloss	ASTM D2457	%	-	85	
Opacity	DIN 53146	%	-	73	78
Whiteness	DIN 5033	%	-	69	74
Yield	ASTM D4321	m <sup>2</sup> /kg	-	37.1	25.6
Density	ASTM D1505	gr/m <sup>3</sup>	-	0.71	
Dynamic C.O.F	ASTM D1894	-	Film-Film	0.4	
			Film-Metal	0.3	

MD: Machine direction, TD: Transverse direction

Available thicknesses: All thicknesses between 35-60 μ can be produced upon request.

POLFILM does not guarantee the typical values. Any data included herein is based on the analysis of representative samples and not the actual product shipped.

POLFILM strongly suggests that before any vast usage, make sure to study "Customer's Guide" and test our product in limited amounts.

NO guarantee is made regarding information presented in this document. The user is solely responsible for all determinations regarding use and therefore POLFILM denies any responsibility for any loss or damage that may occur from the use of this information.

### Storage and Handling:

- Films should be stored on the pallets in a closed dry place and should not be exposed to direct sunlight and heating sources, it means at a safe distance of not less than 1 meter.
- Storage temperature between 10°C to 35°C and in relative humidity less than 60% is recommended in order to minimize the deterioration of the film properties.
- The film should be kept in workplace at least 24 hours before being used.
- It is advisable to manage the inventory according to the delivery dates (first in – first out).
- For more information, please refer to the "customer's guide" document.

### Indication of Surface Treatment:

- POLFILM film is usually supplied with treatment on the outside surface that is indicated on the label of each roll, although all films can be supplied either with treatment on the inside surface. Which should be agreed with our sales department before ordering.

### Printability:


- A standard corona test pen should be used to check surface treatment before use of each roll.
- To check accurately of the surface treatment in laboratory, standard corona solution (ASTM D2578) or contact angle measurement (ASTM D5946) can be used.
- If it is required, customers could do in-line treatment during converting process.

### Standard Roll Dimension:

Core Inner Diameter (inch)	Roll Diameter (mm)	Dimension Width (mm)	Tolerance (mm)
3	520 - 540	30 up to 1650	- 0 & +3
6	720 - 770	280 up to 2400	

### Packaging:

- Films are packed vertically or horizontally on pallets.
- Normally, 6-inch rolls are palletized in horizontal direction and 3-inch rolls are palletized vertically depending on the width.
- For more information, please contact our sales department.



### Food Contact:

- This film complies with EU and FDA regulations. Specific documents and MSDS are available on request.